

## NIEUWE CODENUMMERS

### TELEVISIE

#### Lijnuitgangstransformatoren

TX 1422, TX 1720, 17 TX 111, 21 TX 100	4822 140 10065
14 TX 120, 17 TX 120	4822 140 10019
14 TX 123, 17 TD 120, 17 TX 123, 17 TD 130	4822 140 10021
17 TX 100, 17 TX 112, 21 TX 103, 21 TX 111	4822 140 10022
17 TX 140, 21 TX 140	4822 140 10024
17 TX 144, 21 TX 144, 21 CX 1520	4822 140 10023
17 TX 170, 17 TX 220, 21 TX 170, 21 TX 220 21 TX 240	4822 140 10028
17 TX 250, 17 TX 251, 17 TX 259, 17 TX 291, 21 TX 250, 21 TX 253	4822 140 10012
17 TX 333	4822 140 10015
17 TX 410	4822 140 10042
19 TX 330, 23 TD 336, 23 TX 323, 23 TX 344/79	4822 140 10007
19 TX 391, 23 TI 250, 23 TI 260, 23 TX 392, 23 CX 393	4822 140 10075
23 TX 344, 23 TX 360, 23 TX 362, 23 TX 400, 23 TX 401, 23 TDK 4210	43 296 31
19 TX 410, 19 TX 411, 19 TX 413, 19 TX 441, 23 TX 410, 23 TX 441, 23 TX 442, 23 CX 443, 23 TX 511, 23 TX 512, 23 TX 514, 23 CX 514, 23 CN 376, 23 CCH 444, 23 CCH 514, 25 TX 512, 25 TX 514, CS 2358	4822 140 10063
19 TX 421, 19 TX 491, 23 TX 420, 23 TX 481, 23 TX 482, 23 TX 483, 23 TX 490, 23 TX 550, 23 TX 561, 23 TX 562, 23 TX 563, 23 CX 565, 25 TX 484, 25 TX 485, 25 TX 561, 25 TX 563, 25 TX 564	4822 140 10064
19 TX 430	4822 140 10038
19 TX 500, 19 TX 501, 19 TX 530, 19 TX 531, 19 TX 534, 23 TX 480, 23 TX 501, 23 TX 530, 23 TX 531, 23 CX 541, 23 TX 544, 23 TI 540, 25 TX 543, 25 TX 544	4822 140 10062
21 CX 142, 21 TX 143	4822 140 10025
21 TX 260, 21 TX 262, 17 TX 291 A	4822 140 10003
21 TX 280, 21 TX 281, 21 TX 285, 21 TX 370, 24 TX 300	4822 140 10032
21 TX 290, 21 TD 290, 21 TD 293	4822 140 10068
21 TD 310, 21 TX 310, 31 TX 311, 23 TD 310, 23 TX 310, 23 TX 312, 23 TX 320, 23 TX 322, 23 TX 332, 24 TX 311	4822 140 10005
23 TX 283, 23 TX 302, 23 TX 371, 23 TX 372	4822 140 10001
23 TD 315, 23 TX 315, 23 TX 323/80	4822 140 10055
23 TX 350, 23 TX 351, 23 TX 353, 23 TX 380, 23 TX 381, 23 TX 382, 23 CX 383, 23 TX 460, 23 TX 461, 23 TX 462, 23 CX 463	4822 140 10008
11 LX 520	4822 140 10061
11 LX 522	4822 140 10045
X 19 T 572, X 25 T 573	4822 140 10083
X 19 T 602	4822 140 10082



#### Beelduitgangstransformatoren

TX 400, TX 1422, TX 1720, 14 TX 100	Niet meer leverbaar
17 TX 111, 17 TX 112, 21 TX 100, 21 TX 111, 21 TX 103	
14 TX 120, 14 TX 123, 17 TX 123, 17 TX 140, 17 TX 180, 17 TX 210, 21 TX 120, 21 TX 140, 21 TX 180, 21 TX 210	4822 140 20004
17 TX 144, 17 TX 170, 17 TX 220, 21 TX 144, 21 TX 170, 21 TX 220, 21 TX 230, 21 TX 240	4822 140 20006
17 TX 250, 17 TX 259, 17 TX 291, 17 TX 333, 19 TX 330, 21 TX 250, 21 TX 251, 21 TX 253, 21 TX 260, 21 TX 262, 21 TD 290, 21 TX 290, 21 TD 293, 21 TD 310, 21 TX 311, 23 TI 260, 23 TD 310, 23 TX 310, 23 TX 312, 23 TD 315, 23 TX 315, 23 TX 320, 23 TX 322, 24 TX 311	4822 140 20008
23 TI 250	4822 140 20037
21 TX 280, 21 TX 281, 21 TX 283, 21 TX 285, 21 TX 370, 23 TX 302, 23 TX 371, 23 TX 372, 24 TX 300	4822 140 20009


23 TX 323, 23 TX 332, 23 TX 344, 23 TX 360, 23 TX 362	4822 140 20001
23 TX 323/80, 23 TD 336	4822 140 20001
23 TX 350, 23 TX 351, 23 TX 353, 23 TX 380, 23 TX 381, 23 TX 382, 23 CX 383, 23 TX 460, 23 TX 461, 23 TX 462, 23 CX 463	4822 140 20013
19 TX 391, 19 TX 441, 23 CN 376, 23 CX 393, 23 TX 400, 23 TX 401, 23 TX 441, 23 TX 442, 23 CX 442, 23 CCH 444, 23 TX 511, 23 TX 512 23 TX 513, 25 TX 512, 25 TX 514, 25 CCH 514	4822 140 20027
19 TX 410, 19 TX 411, 19 TX 413, 23 TX 410	4822 140 20029
19 TX 421, 19 TX 491, 23 TX 420, 23 TX 480, 23 TX 481, 23 TX 482, 23 TX 483, 23 TX 490, 23 TX 550, 23 TX 561, 23 TX 562, 23 TX 563, 23 CX 565, 25 TX 484, 25 TX 485, 25 TX 563, 25 TX 564	4822 140 20028
19 TX 430	4822 140 20026
19 TX 500, 19 TX 501, 19 TX 530, 19 TX 531, 19 TX 534, 23 TX 501, 23 TX 530, 23 TX 531, 23 TI 540, 23 CX 541, 23 TX 544, 25 TX 543, 25 TX 544, X 19 T 572, X 19 T 602, X 25 T 573	4822 140 20031
11 LX 522	4822 140 20035
23 TDK 4210	4822 140 20033

### Deflectie-eenheden


17 TX 140, 21 TX 140	4822 150 10011
17 TX 170, 17 TX 180, 17 TX 210, 17 TX 220, 21 TX 170, 21 TX 180, 21 TX 210, 21 TX 220, 21 TX 230, 21 TX 240	4822 150 10013
17 TX 250, 17 TX 259, 17 TX 291, 17 TX 333, 19 TX 330, 19 TX 391, 19 TX 410, 19 TX 411, 19 TX 413, 19 TX 421, 19 TX 441, 21 TX 250, 21 TX 253, 21 TX 260, 21 TX 262, 21 TX 280, 21 TX 281, 21 TX 283, 21 TX 285, 21 TX 290, 21 TX 310, 21 TX 311, 21 TX 370, 23 TX 302, 23 TX 310, 23 TX 312, 23 TX 320, 23 TX 323, 23 TX 332, 23 TX 344, 23 TX 350, 23 TX 351, 23 TX 353, 23 TX 360, 23 TX 362, 23 TX 372, 23 TX 380, 23 TX 381, 23 TX 382, 23 TX 392, 23 TX 400, 23 TX 401, 23 TX 410, 23 TX 420, 23 TX 441, 23 TX 442, 23 TX 460, 23 TX 461, 23 TX 462, 23 TX 480, 23 TX 481, 23 TX 482, 23 TX 483, 23 TX 490, 23 TX 491, 23 TX 511, 23 TX 512, 23 TX 513, 23 TX 550, 23 TX 561, 23 TX 562, 23 TX 563, 23 TI 250, 23 TI 260, 23 TDK 4210 A, 23 CX 383, 23 CX 393, 23 CX 443, 23 CX 463, 23 CX 565, 23 CCH 444 23 CN 376, 24 TX 300, 25 TX 484, 25 TX 485, 25 TX 512, 25 TX 514, 25 TX 562, 25 TX 563, 25 TX 564, 25 CCH 514, CS 2358	4822 150 10024
11 LX 520	4822 150 10034
11 LX 522	4822 150 10049
19 TX 430	4822 150 10056
19 TX 500, 19 TX 501, 23 TX 501	4822 150 10024
19 TX 530, 19 TX 531, 19 TX 534, 23 TX 530, 23 TX 531, 23 CX 541, 23 TX 544, 25 TX 543, 25 TX 544, 23 TI 540, X 19 T 572, X 19 T 602 X 25 T 573	4822 150 10051




4822 140 10042  
A3 570 00  
A3 570 01




4822 140 10062  
3122 108 30630  
3122 108 31400




4822 140 10063  
A3 570 05  
A3 570 06




4822 140 10083  
3122 108 31530




4822 140 10101  
3122 108 31870  
3122 108 33670



4822 140 10104  
3122 108 39090



**ATTENTION:** Replace always the EHT-rectifier valve base by the valve base supplied with the transformer. Otherwise the lifetime of the EHT-rectifier will be shortened considerably.



4822 140 10049  
PK 886 29  
4822 140 10075  
A3 264 11 A3 319 44  
A3 264 12 A3 319 45  
A3 296 31 RK 929 83

4822 140 10007  
A3 160 51 A3 281 76  
A3 160 52 KR 359 76  
A3 178 41 3W 008 91





4822 140 10015  
A3 504 77  
3W 018 84

4822 140 10005  
A3 300 60

4822 140 10005  
A3 091 31  
A3 155 21

4822 140 10005  
KR 359 69  
KR 359 70

CS40655



4822 727 10673/CS04