

#### TYPE 7BAP-

The Du Mont Type 7BAP- is a 4 x 6-inch rectangular, dual beam, electrostatic focus and deflection cathode-ray tube. Post acceleration is used to obtain maximum deflection sensitivity with high brightness. The electron gun structures are so designed as to require no appreciable focusing current. The deflection-electrode connections are brought out through the neck to minimize lead inductance and capacitance and to improve insulation.

## GENERAL CHARACTERISTICS 1

#### Electrical Data

Focusing Method Deflecting Method	· · · · · · · · · · · · · · · · · · ·		Electrostatic Electrostatic	
Direct Interelectrode Co	apacitances Appr	oximate		
	Cathode to all other electrodes			μ <del>μ</del> f
Grid No. 1 to all off	Grid No. 1 to all other electrodes			μμf
D1 to D2			1.5	μμf
D3 to D4			1.5	μμf
D1 to all other electrodes except D2			2.4	μμf
	D2 to all other electrodes except D1			μμf
D3 to all other electrodes except D4			2.4 2.4	μμf
D4 to all other electrodes except D3		2.4	μµf	
Optical Data				
Phosphor Number	P1	P2	P7	P11
Fluorescence	Green	Blue-Green	Blue-White	Blue
Phosphorescence		Green	Yellow	
Persistence	Medium	Long	Long	Short
Mechanical Data				
Overall Length			18 1/4± 1/4	Inches
Greatest Bulb Dimension	1			
Width			6 1/16 ± 1/32	Inches
Height			4 1/16 ± 1/32	Inches
Minimum Useful Screen	Dimensions		5 1/4	
	Width			Inches
Height			3 1/4	Inches
Bulb Contact			J1-22	
Neck Contacts			C1-2	
Base			B12-37	
Allen B. Du Mont Laboratories, Inc.			DE-5579 - 2	
Clifton, New Jersey			4/13/60	FORM 809 M1 9 89 8H



### TYPE 7BAP-

## GENERAL CHARACTERISTICS (MECHANICAL DATA) (Continued)

Basing	14 K	
Base Alignment:	• •	_
D1D2 trace aligns with Base Key and Tube Axis	± 10	Degrees
Positive voltage on D1 deflects beam approximately to		
Positive voltage on D3 deflects beam approximately to	ward Pin No. 11.	
Bulb Contact Alignment:		_
J1-22 contact aligns with D1D2 trace	± 10	Degrees
J1-22 contact located on tube center line	± 1/4	Inch
J1-22 contact on same side as Base Key		
Trace Alignment:		
Angle between D1D2 and D3D4 traces	90 ± 1 1	Degrees Degree
Corresponding traces of each gun align within		
D3D4 trace aligns with Bulb Side Wall	3	Degrees
MAXIMUM RATINGS (ABSOLUTE VALUES)		
Heater Voltage	6.3	Volts
Heater Current at 6.3 Valts	0.6 ± 10%	Ampere
Post Accelerator Voltage	8, 250	Max. Volts DC
Accelerator Voltage 2	2,750	Max. Volts DC
Accelerator Input	6	Max. Watts
Ratio Post Accelerator Voltage to Accelerator Voltage 2	3.0	Max.
Focusing Voltage	1, 100	Max. Volts DC
Grld No. 1 Voltage	7, 100	11.0X, 70113 5 G
Negative Bias Value	200	Max, Volts DC
Positive Bias Value	0	Max. Volts DC
Positive Peak Value	Ö	Max. Volts
Peak Heater to Cathode Voltage	V	14/UA. 40(13
Heater Negative with respect to Cathode	180	Max. Volts
Heater Positive with respect to Cathode	180	Max. Volts
	100	MITTY AGELZ
Peak Voltage between Accelerator and any Deflection— Electrode	600	Max. Volts
TYPICAL OPERATING CONDITIONS 1		man, veno
Book Appelon to Walking	4 000	V 16- 00
Post Accelerator Voltage	4,000	Volts DC
Accelerator Voltage	2,000	Volts DC
Focusing Voltage	363 to 695	Volts DC
Grid No. 1 Voltage 3	-45 to -75	Volts DC
Modulation <sup>4</sup>	42	Max. Volts DC
en B. Du Mont Laboratories, Inc.	DE-5579 - 2	
ifton, New Jersey		FORM 509 M1 3 59 6H
•		FURN DUE MI 2 DE EN



#### TYPE 7BAP-

#### TYPICAL OPERATING CONDITIONS (Continued)

Line Width "A" <sup>4</sup> Deflection Factors: 8	0.70	Max. MM
D1 and D2	84 to 102	Volts DC/Inch
D3 and D4	67 to 81	Volts DC/Inch
Interaction Factor <sup>5</sup> Spot Position <sup>6</sup>	$14 \times 10^{-6}$	Inch/Volt DC Max.
Deflection Factor Uniformity <sup>7</sup>	2%	Max.

## MAXIMUM CIRCUIT VALUES 1


Grid No. 1 Circuit Resistance	1.5	Max, Megohms
Resistance in any Deflection-Electrode Circuit	5.0	Max. Megohms

#### NOTES

- 1. Values are for each unit unless otherwise stated.
- 2. This tube is designed for optimum performance when operating at an Eb3/Eb2 ratio of 2.0. Operation at other ratios of Eb3/Eb2 may result in changes in deflection uniformity and pattern distortion.
- Visual extinction of the focused, undeflected spot.
- 4. Measured in accordance with MIL-E-1 specifications, using a beam current of 25 μADC.
- 5. The deflection of one beam when balanced DC voltages are applied to the deflection electrodes of the other beam will not be greater than the indicated value.
- 6. With the tube shielded against external influences, and the deflecting electrodes connected to the accelerator, the undeflected and focused spot will fall within a 15-mm square centered on the tube face, one side of which is parallel to the D3D4 trace.
- 7. The deflection factor (for both DID2 and D3D4 plate pairs, separately) for any deflection of less than 75% of the useful screen will not differ from the deflection factor for a deflection at 25% of the useful screen by more than the indicated value.
- Ratio of deflection factors of corresponding sets of deflection plates (larger deflection factor divided by lower deflection factor) will not excel 1.15.
- 9. It is recommended that the deflection-electrode circuit resistances be approximately equal.

DE-5579 - 2

# MOMUD



#### NOTES:

- 1.DI D2TRACE TO ALIGN WITH J1-22 CAP AND BASE KEY±10°
- 2.JI-22 CAP LOCATED ON TUBE CENTER LINE ± 1 INCH